

N-LASF40 834373.443

$n_d = 1,83404$	$v_d = 37,30$	$n_F - n_C = 0,022363$
$n_e = 1,83935$	$v_e = 37,04$	$n_F' - n_C' = 0,022658$

Brechzahlen		
	λ [nm]	
$n_{2325,4}$	2325,4	1,78600
$n_{1970,1}$	1970,1	1,79298
$n_{1529,6}$	1529,6	1,80074
$n_{1060,0}$	1060,0	1,80999
n_i	1014,0	1,81118
n_e	852,1	1,81643
n_f	706,5	1,82380
n_C	656,3	1,82745
$n_{C'}$	643,8	1,82849
$n_{632,8}$	632,8	1,82946
n_D	589,3	1,83385
n_d	587,6	1,83404
n_e	546,1	1,83935
n_F	486,1	1,84981
$n_{F'}$	480,0	1,85114
n_g	435,8	1,86275
n_h	404,7	1,87393
n_i	365,0	
$n_{334,1}$	334,1	
$n_{312,6}$	312,6	
$n_{296,7}$	296,7	
$n_{280,4}$	280,4	
$n_{248,3}$	248,3	

Konstanten der Dispersionsformel	
B_1	1,98550331
B_2	0,274057042
B_3	1,289456610
C_1	0,01095833100
C_2	0,0474551603
C_3	96,9085286

Konstanten der Formel für dn/dT	
D_0	8,10E-06
D_1	1,25E-08
D_2	-1,73E-11
E_0	8,27E-07
E_1	1,08E-09
λ_{TK} [μ m]	0,238

Temperaturkoeffizienten der Lichtbrechung						
[°C]	$\Delta n_{rel}/\Delta T$ [$10^{-6}/K$]			$\Delta n_{abs}/\Delta T$ [$10^{-6}/K$]		
	1060.0	e	g	1060.0	e	g
-40/-20	7,1	8,8	10,6	4,6	6,3	8,0
+20/+40	7,3	9,3	11,4	5,7	7,7	9,8
+60/+80	7,6	9,7	12,0	6,3	8,5	10,8

Reintransmissionsgrad τ_i		
λ [nm]	τ_i [10mm]	τ_i [25mm]
2500	0,570	0,240
2325	0,810	0,590
1970	0,963	0,910
1530	0,993	0,982
1060	0,998	0,995
700	0,998	0,996
660	0,998	0,994
620	0,997	0,993
580	0,997	0,992
546	0,995	0,988
500	0,987	0,969
460	0,973	0,930
436	0,954	0,890
420	0,940	0,850
405	0,910	0,780
400	0,890	0,750
390	0,840	0,650
380	0,760	0,510
370	0,600	0,280
365	0,470	0,150
350	0,040	
334		
320		
310		
300		
290		
280		
270		
260		
250		

Farbcode	
$\lambda_{80} / \lambda_{5}$	39/35*

Bemerkungen	
(*= λ_{70}/λ_5)	

Relative Teildispersionen	
$P_{s,t}$	0,2346
$P_{C,s}$	0,4929
$P_{d,C}$	0,2948
$P_{e,d}$	0,2371
$P_{g,F}$	0,5786
$P_{i,h}$	
$P'_{s,t}$	0,2315
$P'_{C,s}$	0,5321
$P'_{d,C'}$	0,2453
$P'_{e,d}$	0,2340
$P'_{g,F'}$	0,5124
$P'_{i,h}$	

Abweichung relativer Teildispersionen ΔP von der "Normalgeraden"	
$\Delta P_{C,t}$	0,0055
$\Delta P_{C,s}$	0,0030
$\Delta P_{F,e}$	-0,0007
$\Delta P_{g,F}$	-0,0024
$\Delta P_{i,g}$	

Sonstige Eigenschaften	
$\alpha_{-30/+70^\circ C}$ [$10^{-6}/K$]	5,8
$\alpha_{+20/+300^\circ C}$ [$10^{-6}/K$]	6,9
T_g [°C]	590
T_{10}^{-13} [°C]	591
$T_{10}^{7,6}$ [°C]	677
c_p [J/(g·K)]	0,550
λ [W/(m·K)]	0,810
ρ [g/cm ³]	4,43
E [10^3 N/mm ²]	111
μ	0,304
K [10^{-6} mm ² /N]	2,19
$HK_{0,1/20}$	580
HG	1
CR	1
FR	1
SR	51,2
AR	1
PR	1,3